



6P23 6P25 6P27 6P29



Attached Stem **SR621SW** Ф23.7



Small **0.02** 24 Hour **0.137** (Except 6P25)

case 0.45mm Clearance Clearance changes subject to the glass, case structure, and **Movement** the length of the hand. \$ 0.15 ~ 0.30mm

1,000 pcs

Original Package

Time measurement


Accuracy

Balance Weight

<µN⋅m>

The unit (gate) time of measurement must be set at "10 sec." and the measurement must be performed in the form of complete watch.

10 sec 10 sec 10 sec



Month

24 Hour

High Hand Ver. 6P79

